

258573-000 | FOSC-OC-6CLX551NN

FOSC® A-TRAY-24 type, CWDM, 3 channels + upgrade port, double demux, 20 nm channel spacing, 1533.47 nm starting wavelength



Product Classification

Regional Availability	North America
Product Type	CWDM splice tray
Product Brand	FOSC®
Product Series	FOSC-OC

General Specifications

Application	For use in FOSC closures
Interface, Input	Stub tail
Interface, Output	Stub tail

Dimensions

Height	233.68 mm 9.2 in
Width	99.06 mm 3.9 in
Depth	10.67 mm 0.42 in

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

