



Black 2 in PVC Tape, 20 ft

## Product Classification

<b>Product Type</b>	Weatherproofing tape
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Application</b>	Provides additional moisture seal for cable connections
<b>Applications per Kit</b>	Four 1/2 in–1/2 in   Four 1/2 in–7/8 in to device   One 1/2 in–2-1/4 in   Two 1/2 in–7/8 in
<b>Color</b>	Black

## Dimensions

<b>Width</b>	50.8 mm   2 in
<b>Length</b>	6096 mm   240 in
<b>Nominal Size</b>	1-1/4 in   1-5/8 in   1/2 in   1/4 in   2-1/4 in   3/8 in   5/8 in   7/8 in

## Material Specifications

<b>Material Type</b>	PVC tape
----------------------	----------

## Environmental Specifications

<b>Operating Temperature</b>	-10 °C to +80 °C (+14 °F to +176 °F)
<b>UV Resistance Test Method</b>	PVC tape test method UL 510, ASTM D1000
<b>Weather Resistance Test Method</b>	04AS00-03.6.0   MIL-STD-1344A, Method 1002

## Packaging and Weights

<b>Height, packed</b>	63.5 mm   2.5 in
<b>Width, packed</b>	63.5 mm   2.5 in
<b>Length, packed</b>	50.8 mm   2 in

# 9905-71

---

**Packaging quantity** 1  
**Weight, gross** 0.08 kg | 0.176 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system