


# 204673-24

---



Twenty four 4" Port Entrance Panel, 4" x 6"

## Product Classification

<b>Product Type</b>	Entrance panel
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Color</b>	Gray
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Number of Ports</b>	24
<b>Panel Type</b>	Multiple

## Dimensions

<b>Height</b>	787.4 mm   31 in
<b>Width</b>	1,003.3 mm   39.5 in

## Material Specifications

<b>Material Type</b>	Aluminum
----------------------	----------

## Environmental Specifications

<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

## Packaging and Weights

<b>Height, packed</b>	668.02 mm   26.3 in
<b>Width, packed</b>	459.74 mm   18.1 in
<b>Length, packed</b>	50.8 mm   2 in
<b>Included</b>	Entry cap   Hardware   Port
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	2.5 kg   5.512 lb

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

## Included Products

CAP-4 – Snap-in Entry Port Cap, 4"

# CAP-4

---



## Snap-in Entry Port Cap, 4"

### Product Classification

<b>Product Type</b>	Port cap
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

### General Specifications

<b>Color</b>	Black
<b>Entry Panel Port Size</b>	101.6 mm   4 in
<b>Panel Type</b>	Multiple

### Material Specifications

<b>Material Type</b>	Engineered plastic
----------------------	--------------------

### Packaging and Weights

<b>Height, packed</b>	127 mm   5 in
<b>Width, packed</b>	127 mm   5 in
<b>Length, packed</b>	248.92 mm   9.8 in
<b>Included</b>	Entry cap
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	0.02 kg   0.044 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

