

243095-7



Stainless Steel Hardware Kit for 4 mm, 3/8 in, 5/8 in, 1/2 in or 7/8 in Block style hangers, includes M10 bolts and hardware, 140.97 mm (5.55 in) length

Product Classification

Product Type	Hardware kit
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Thread Size M10

Dimensions

Maximum Stack Height	2
Length	140.97 mm 5.55 in
Nominal Size	1/2 in 7/8 in

Material Specifications

Material Type Stainless steel 304

Packaging and Weights

Height, packed	60.96 mm 2.4 in
Width, packed	20.32 mm 0.8 in
Length, packed	20.32 mm 0.8 in
Included	Fifty flat washers Ten M10 threaded rods Thirty hex nuts Twenty lock washers
Packaging quantity	10
Weight, gross	1.388 kg 3.06 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power