



Lace-up Hoisting Grip for HELIAX® 1.50-1.74 in (38.1-63.5 mm) cables and elliptical waveguide 37

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	660.4 mm 26 in
Leader Length, minimum	355.6 mm 14 in
Compatible Diameter, maximum	63.5 mm 2.5 in
Compatible Diameter, minimum	50.8 mm 2 in
Nominal Size	2-1/4 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel Tin-coated bronze
----------------------	-------------------------------------

Mechanical Specifications

Pull Load Capacity	526.167 kg 1160 lb
---------------------------	----------------------

31535

Packaging and Weights

Height, packed	388.62 mm 15.3 in
Width, packed	83.82 mm 3.3 in
Length, packed	388.62 mm 15.3 in
Packaging quantity	1
Weight, gross	0.77 kg 1.698 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

