DFJ-2M5-NBS



HELIAX® Discrete, 2 multimode fiber, 5 mm LSZH cable. End 1: DLC with weatherproofing boot. End 2: DLC with uniboot

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Wireless Fiber Cable Assemblies

Product Brand HELIAX®
Product Series DFJ

Ordering Note ANDREW® non-standard product

General Specifications

Construction Type Discrete fiber tail

Interface, Connector A DLC

 Interface Feature, connector A
 Nokia boot

 Interface Body Style, connector A
 Straight

 Interface, Connector B
 DLC

 Interface Feature, connector B
 Uniboot

Interface Body Style, connector B Straight

Jacket Color Black

Total Fibers, quantity 2

Dimensions


Cable Assembly Length Range (m) 3 - 50

Diameter Over Jacket 5 mm | 0.197 in

Ordering Tree



DFJ-2M5-NBS



Material Specifications

Jacket Material Low Smoke Zero Halogen (LSZH)

Optical Specifications

Fiber Mode Multimode

Fiber Type OM2, bend insensitive

Insertion Loss, typical note Insertion loss is measured at 850 nm

Insertion Loss, typical 0.5

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Environmental Space Outdoor

Packaging and Weights

Cable weight 25 kg/km | 16.799 lb/kft

* Footnotes

Insertion Loss, typical note Insertion loss is measured at a room temp of +20°C (+68°F)

