

# SSC-760249586X1 | Radio Enclosure MV2



## Future Ready Middle of the Pole Concealment for Samsung, Nokia, and Ericsson equipment

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

Includes mounting hardware for clamp on, through-bolt, or banding to poles or structures.

Available After Market Kits -- ordered separately:

-860661823S-xx Wood Pole 5" Standoff

-860661823ST-xx Round Tapered Pole 5" Standoff

-860661736-MV2-C01x Ice Canopy

-860661736-MV2-C02 Delta 3.0 rectifier mount kit

-860661736-MV2-C03x DBHP & MV2 Fan Tray Kit (x = color)

-860661736-MV2-C07 Nokia AZHL & APAM PSU

-860661736-MV2-C020 for Samsung Gen 2 ORAN radios

-860661736-MV2-C09x for 4435/4449/4478/4890 radios & AC08 or 6308 PSU's. Includes fan tray kit and fan. Select "x" to match color of enclosure.

## Product Classification

<b>Product Type</b>	Mid pole
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Black Green (RAL 6012)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)   White (RAL 9010)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	6304   6308   ABB CC1600   APAM   CCI PSU-1200W-48-N   DELTA 2.0   DELTA 3.0   PSU-AC-08
<b>Radio Compatibility, Ericsson</b>	220x   440x   4415   4426   4435   4449   4455   4478   4890   8843   8863
<b>Radio Compatibility, Nokia</b>	AHBCA   AHGCC   AHFIA   AHFIB   AHFIC   AHLBA   AHLBBA   AWHQN   AZHL   Diplexer

# SSC-760249586X1 | Radio Enclosure MV2

---

**Radio Compatibility Samsung** RF4402D-D1A | RF4439D | RF4440D | RF4461D | RFV01U-D1A | RFV01U-D2A | RT2201-46A | RT4401-48A | RT4423-48A

**Radios Included** None

## Dimensions

**Height** 1,219.2 mm | 48 in

**Width** 609.6 mm | 24 in

**Depth** 635 mm | 25 in

## Electrical Specifications

**Power/Fiber Input** Trade size knockouts at rear side

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.49 m<sup>3</sup> | 17.3 ft<sup>3</sup>

**Weight (loaded)** 215.456 kg | 475 lb

**Weight (unloaded)** 31.751 kg | 70 lb