

NG4-CBOUT-1728

Fiber Optic Ribbon Breakout Kit, High Density, 1:3, 288f in - 96f x 3 out;
6 kits for up to 1728f Cable



Product Classification

Regional Availability	Latin America North America
Product Type	Fiber breakout kit, rectangular

General Specifications

Application	For use with ribbon fiber cables
Breakout Legs, quantity	3
Fibers per Ribbon, maximum	36
Fibers per Tube, maximum	288
Tubes per Leg, quantity	3

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---