


BUDI-R24NP0309A | BUDI-R24NP0309A



BUDI™ Rapid Terminal, 24-position, SC/UPC, Indoor plenum cable, MPO at far end, 100 ft

- Designed to provide a quick and simple solution for installing fiber in small and medium sized MDU's
- Incorporates a unique fiber cable spooling system that stores up fiber cable within the enclosure
- Removes the need for field termination and extensive site survey inspections

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Australia/New Zealand Europe North America |
| Portfolio | CommScope® |
| Product Type | Rapid distribution terminal |
| Product Brand | BUDI™ RapidReel® |
| Product Series | BUDI-R |
| Warranty | For more information, please consult our Product Warranty guidelines |

General Specifications

| | |
|-----------------------------|------------------------------|
| Functionality | Patching Slack storage |
| Adapters, quantity | 24 |
| Cable Entry Location | Bottom |
| Cable Sealing Type | Gasket/grommet configuration |
| Cable Type | Indoor - Stranded |
| Color | Gray |
| Distribution Type | 24 ports |
| Interface | SC/UPC |
| Interface, stub | MPO |
| Lock Type | Security screw |
| Mounting | Wall mount |
| Port, quantity | 24 |

Dimensions

| | |
|---------------|-------------------|
| Height | 270 mm 10.63 in |
| Width | 214 mm 8.425 in |

BUDI-R24NP0309A | BUDI-R24NP0309A

| | |
|-----------------------|-------------------|
| Depth | 125 mm 4.921 in |
| Cable Length | 30 m 98.425 ft |
| Enclosure Size | Small |

Material Specifications

| | |
|----------------------|----------------------------|
| Material Type | Polycarbonate ABS (PC-ABS) |
|----------------------|----------------------------|

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | G.657.A2 |

Environmental Specifications

| | |
|--------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +65 °C (-40 °F to +149 °F) |
| Environmental Space | Indoor/Outdoor |
| Flammability Rating | UL 94 V-0 |
| Qualification Standards | IEC 61753-1 UL |

Packaging and Weights

| | |
|---------------------------|--------|
| Packaging quantity | 1 |
| Packaging Type | Carton |

* Footnotes

| | |
|-----------------|--|
| Warranty | For more information, please consult our Product Warranty guidelines |
|-----------------|--|