



MPO Fanout Cable, polarity A, 12 fiber MPO (unpinned) to LC duplex, Plenum 3mm SM, 6m, with 36" breakout

## Product Classification

|                              |                               |
|------------------------------|-------------------------------|
| <b>Regional Availability</b> | Latin America   North America |
| <b>Portfolio</b>             | CommScope®                    |
| <b>Product Type</b>          | Fiber fanout cable assembly   |
| <b>Product Brand</b>         | MPOptimate®                   |
| <b>Product Series</b>        | MPA                           |

## General Specifications

|                                       |                           |
|---------------------------------------|---------------------------|
| <b>Connector A, quantity</b>          | 1                         |
| <b>Color, boot A</b>                  | Black                     |
| <b>Color, connector A</b>             | Green                     |
| <b>Connector B, quantity</b>          | 12                        |
| <b>Color, boot B</b>                  | Blue                      |
| <b>Color, connector B</b>             | Blue                      |
| <b>Construction Type</b>              | Plug-and-play, array cord |
| <b>Interface, Connector A</b>         | MPO-12/UPC Female         |
| <b>Interface Feature, connector A</b> | Unpinned                  |
| <b>Interface, Connector B</b>         | LC/UPC                    |
| <b>Jacket Color</b>                   | Yellow                    |
| <b>Total Fibers, quantity</b>         | 12                        |

## Dimensions

|                    |                 |
|--------------------|-----------------|
| <b>Cord Length</b> | 6 m   19.685 ft |
|--------------------|-----------------|

## Optical Specifications

|                   |            |
|-------------------|------------|
| <b>Fiber Mode</b> | Singlemode |
| <b>Fiber Type</b> | OS2        |

## Environmental Specifications

**Environmental Space** Plenum

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |

## Included Products

- 760237964 P-012-MP-8G1-F30YL - Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 12 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
- 860637435 - LC/UPC Connector, Singlemode, Blue, Short Boot
- 860638318 - MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm