SFG23HDX-10-3-126



G23HDX High Capacity Sector Frame, 10.5 ft x 2.88 in OD face pipes, includes three 2.88 OD x 126 in antenna pipes.

Product Classification

Product Type	High capacity Tower sector frame
Ordering Note	NSTD445 Compliant

General Specifications

Application	4G LTE antenna/radio mount
Mounting	Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	3
Tower Taper	Non-tapered | Tapered

Dimensions

Height	3,200.4 mm | 126 in
Face Width	3.2 m | 10.5 ft
Width	3,200.4 mm | 126 in
Pipe Length	3,200.4 mm | 126 in
Face Support Pipe Diameter	73.025 mm | 2.875 in
Mounting Diameter, maximum	218.44 mm | 8.6 in
Mounting Diameter, minimum	38.1 mm | 1.5 in
Pipe Outer Diameter	73.025 mm | 2.875 in
Stand-off Distance	1,239.52 mm | 48.8 in

Material Specifications

Material Type	Hot dip galvanized steel

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222-G

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024

SFG23HDX-10-3-126

Packaging and Weights

Included	Frame | Pipe mounts | Plain end pipes (3) | Stiff arm | Tower attachment
Packaging quantity	1
Weight, net	366.956 kg | 809 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024