760087593 | RFE-MOD-024-5K-MPO-LC02-KGR



Product Classification

ReadyPATCH® Multimode OM4 Keyed Module, 24 LC ports, green

• Part of the Uniprise® ReadyPATCH® Pre-terminated Fiber line

North America
CommScope®
Fiber module
LazrSPEED® ReadyPATCH®
Breakout
12
2
Green
Gray
LC/UPC
Keyed
MPO
Male
Method B
Yes
24
24
27.94 mm 1.1 in

Height	27.94 mm 1.1 in
Width	129.54 mm 5.1 in
Depth	127 mm 5 in

Optical Specifications

Fiber Mode

Multimode

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 22, 2023



760087593 | RFE-MOD-024-5K-MPO-LC02-KGR

550

Fiber Type	OM4, LazrSPEED®
Insertion Loss Change, mating	0.3 dB
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.9 dB

Environmental Specifications

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant

1



Included Products

460117401

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Green

* Footnotes

Insertion Loss Change, mating Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 22, 2023



460117401

LazrSPEED® LC Duplex Hybrid Keyed Adapter, Green

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America	
Portfolio	CommScope®	
Product Type	Fiber adapter	
Product Brand	LazrSPEED®	

General Specifications

Body Style	Duplex
Color	Green
Interface	LC/UPC
Interface Feature	Keyed
Mounting	No flange
Shuttered	No
Total Ports, quantity	2
Transmission Standards	TIA/EIA-568-B.3 TIA/EIA-604 FOCIS-3

Material Specifications

Alignment Sleeve Material Zirconia

Optical Specifications

Fiber Mode Multimode | Singlemode

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency

Classification

1

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system



Page 3 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 9, 2023

