


760109306 | 360G2 Cassette 6-SC-MM-BG



SYSTIMAX 360G2 Cassette 6 SC OptiSPEED® Beige

OBSOLETE

This product was discontinued on: October 16, 2017

Replaced By:

760109298 360G2 Multimode OM4 Fiber Cassette 6 SC no pigtails
360G2 Cartridge 6-SC-LS-AQ

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette
Product Brand	OptiSPEED® SYSTIMAX 360™

General Specifications

Adapter Color	Beige
Interface, front	SC/UPC
Interface, rear	No pigtail
Total Fibers, quantity	0
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in

Environmental Specifications

Safety Standard	UL
------------------------	----

760109306 | 360G2 Cassette 6-SC-MM-BG

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications


Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

700206956 – OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack
MFA-SC06-BG-SHUTTERED

700206956 | MFA-SC06-BG-SHUTTERED



OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	OptiSPEED®
Product Series	MFA

General Specifications

Body Style	Ganged
Color	Beige
Interface	SC/UPC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	6

Material Specifications

Alignment Sleeve Material	Zirconia (ceramic)
----------------------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

700206956 | MFA-SC06-BG-SHUTTERED

UK-ROHS

Compliant

