

760034090 | MODG2-6SC-MM-PT-B



G2 Modular Cassette with 6 SC OptiSPEED® Multimode Pigtails, Type B

OBSOLETE

Replaced By:

760109546

360G2 Cassette 6-SC-MM-BG-Pigtails B

SYSTEMAX 360G2 Cassette 6 SC OptiSPEED® Beige with Pigtails B

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTEMAX®
Product Type	Fiber cassette with pigtails
Product Brand	OptiSPEED®

General Specifications

Adapter Color	Beige
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	OM1
Insertion Loss, typical	0.3 dB
Return Loss, minimum	20 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification


ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

700206956 – OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack
MFA-SC06-BG-SHUTTERED

700206956 | MFA-SC06-BG-SHUTTERED



OptiSPEED® SC Multiport Shuttered Adapter, Beige, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	OptiSPEED®
Product Series	MFA

General Specifications

Body Style	Ganged
Color	Beige
Interface	SC/UPC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	6

Material Specifications

Alignment Sleeve Material	Zirconia (ceramic)
----------------------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

UK-ROHS

Compliant

