


UHXQXQXQF



Ultra Low Loss (ULL) OM4 MPO8 QSFP (Pinned) to MPO8 QSFP (Pinned), Armored Fiber Trunk Cable Assembly, 24-Fiber, Plenum

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Asia Australia/New Zealand Europe Latin America Middle East /Africa North America |
| Portfolio | CommScope® |
| Product Type | Fiber trunk cable assembly |
| Product Brand | SYSTIMAX ULL |
| Ordering Note | For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

General Specifications


| | |
|---------------------------------------|---|
| Color, boot A | Gray |
| Color, boot B | Gray |
| Color, connector A | Aqua |
| Color, connector B | Aqua |
| Construction Type | Stranded Ultra Low Loss (ULL) armored trunk/extension/cross-connect, indoor |
| Fibers per Subunit, quantity | 8 |
| Furcation Color | Aqua |
| Interface, Connector A | MPO-08/UPC Male |
| Interface Feature, connector A | QSFP configuration |
| Interface, Connector B | MPO-08/UPC Male |
| Interface Feature, connector B | QSFP configuration |
| Jacket Color | Aqua |
| Polarity | Method B Enhanced (ULL) |
| Total Fibers, quantity | 24 |

UHXQXQXQF

Dimensions

| | |
|---|----------|
| Breakout Length | 33 in |
| Cable Assembly Length Range (m) | 3 – 999 |
| Cable Assembly Length Range (ft) | 10 – 999 |

Ordering Tree



Mechanical Specifications

| | |
|--|---------------------------------|
| Cable Retention Strength, maximum | 11.24 lb @ 0 ° 4.40 lb @ 90 ° |
|--|---------------------------------|

Optical Specifications

| | |
|-------------------|-----------------|
| Fiber Mode | Multimode |
| Fiber Type | OM4, LazrSPEED® |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Environmental Space | Plenum |

Included Products

| | | |
|--------------------------------|---|--|
| 760119818 P-024-MZ-5K-F12AQ | - | LazrSPEED® Plenum MPO Trunk Cable, interlocking aluminum armored with plenum jacket, 24 fiber with 12 fiber subunits |
| 860633308 | - | MPO8, ULTRA LOW LOSS, MALE, OM3/4, AQUA, 3m |