

# FGS-HTBK-18-5-80PC



FiberGuide® 18in Horizontal Tool-less Bracket Kit for 4x12,4x18 and 4x24 Systems, 5in Tall, kit of 80

This 18in bracket attaches to 18in ladder rack using our tool-less Quick Knobs. Used to mount and support 4x12 and 4x18in FiberGuide® above ladder racking. Ships in a kit of 80 brackets.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

## General Specifications

<b>Color</b>	Black
<b>Note</b>	Includes fastening hardware
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket
<b>Bracket Type</b>	Center Support
<b>Bracket Installation Type</b>	N/A
<b>Attachment Type</b>	Ladder rack

## Dimensions

<b>Height</b>	171.501 mm   6.752 in
<b>Width</b>	114.3 mm   4.5 in
<b>Length</b>	460.096 mm   18.114 in
<b>Thread Size</b>	N/A
<b>System Dimensions</b>	102 mm x 305 mm (4 in x 12 in)   102 mm x 457 mm (4 in x 18 in)   102 mm x 610 mm (4 in x 24 in)

## Packaging and Weights

<b>Packaging quantity</b>	80
---------------------------	----

# FGS-HTBK-18-5-80PC

---

**Weight, net**

87.561 kg | 193.04 lb

## Included Products

HDW-12021 – FiberGuide® Quick Knob with T-Bolt

# HDW-12021

---



## FiberGuide® Quick Knob with T-Bolt

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber raceway hardware
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS
<b>Minimum Order Quantity</b>	10

### General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Accessory

### Dimensions

<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)   51 mm x 152 mm (2 in x 6 in)
--------------------------	--

### Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.015 kg   0.033 lb

### Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# HDW-12021

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

