



OFDC B8G Fiber Optic Splice/Patch Closure, X-press version, Gel Cable sealing, 1 pre-installed 18-fiber splice tray, 8 duplex LC/APC adapters, 20 m drop cable assy, mobra

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Series</b>	OFDC

## General Specifications


<b>Cable Ports Quantity, total</b>	4 round ports + 8 round ports
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Manhole   Pedestal   Strand   Wall
<b>Port Type</b>	LC/APC
<b>Splice Tray Included, quantity</b>	1
<b>Splice Tray Type Included</b>	18-way, heat shrink
<b>Splitter Type</b>	No splitter
<b>Splitter, quantity</b>	0

## Dimensions

<b>Height</b>	128 mm   5.039 in
<b>Width</b>	156 mm   6.142 in
<b>Length</b>	324 mm   12.756 in

# 1155163-2 | OFDC-B8G-RAT-16F-20M-KIT-NZ1

## Ordering Tree



## Material Specifications

**Material Type** Rugged polymer

## Environmental Specifications

**Installation temperature** -5 °C to +45 °C (+23 °F to +113 °F)

**Storage Temperature** -30 °C to +60 °C (-22 °F to +140 °F)

**Relative Humidity** 93%, non-condensing

**Environmental Space** Above ground | Below ground

**Qualification Standards** IEC 60529, IP68 + 2 m waterhead

**UV Resistance** UV stabilized

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# 1155163-2 | OFDC-B8G-RAT-16F-20M-KIT-NZ1

---

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

