42396A-16



Product Classification

Butterfly Hanger for elliptical waveguide 43

Product Type	Hanger kit
Ordering Note	CommScope® non-standard product
General Specifications	
Cable Type	Elliptical waveguide
Cables per Hanger	1
Color	Silver
Hanger Type	Standard butterfly hanger
Mounting	3/8 in (M10) drilled cable ladder
Dimensions	

Maximum Stack Height	0
Height	41.9 mm 1.65 in
Width	38.1 mm 1.5 in
Length	63.5 mm 2.5 in
Compatible Cable Diameter Range	34.8-38.6 mm
Compatible Diameter, maximum	38.6 mm 1.52 in
Compatible Diameter, minimum	34.8 mm 1.37 in
Waveguide Size	WR187 WG12 R48
Electrical Specifications	

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dBMaterial Specifications

Material Type

Stainless steel

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024



42396A-16

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
Environmental Specifications	
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degredation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
Packaging and Weights	
Height, packed	26 cm 10.236 in
Width, packed	8.9 cm 3.504 in
Length, packed	8.9 cm 3.504 in
Packaging quantity	10
Weight, gross	0.76 kg 1.676 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

* Footnotes

9001:2015

Maximum Stack Height Fiber, Hybrid, Power

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2024

COMMSCOPE°