

SSC-760236577N2U



Top of Pole 18in Dia Concealment Enclosure for up to three Nokia Metro Cell radios Or Samsung LAA/CBRS

- Enclosure for holding up to 3 Nokia metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment with a shroud that is 18" in diameter and 65" tall that can accommodate CommScope as well as most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

-Supports AWHQN with separately available kit "860665079-AMK-001"

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket
Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

See compatibility matrix for compatible antennas

Product Classification

Portfolio	CommScope®
Product Type	Pole top
Product Brand	Metro Cell
Ordering Note	CommScope® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, CommScope	CommScope Canister Antennas
Antenna Compatibility, Other Vendors	ACE AMPHENOL DK GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERGER
Antennas Included	None
Color	Light Gray (RAL 7035)
Color Options	Beige-Grey (RAL 7006) Black (RAL 9005) Brown (RAL 8014) Faux Concrete Green (RAL 6005) Metallic Silver
Cooling	Passive Cooling
Mounting Options	Non-tapered poles Tapered poles Wood poles
Radio Compatibility, Nokia	(3) Airscale micro radios (Including LAA & CBRS models) AHIA AHIB AWHQN AZRB Airscale

SSC-760236577N2U

micro | Diplexer | Power Distribution

Radio Compatibility Samsung

Diplexer | Power Distribution | RT2201-46A | RT4401-48A

Radios Included

None

Dimensions

Height

1,651 mm | 65 in

Width

457.2 mm | 18 in

Depth

457.2 mm | 18 in

Mounting Bolt Circle Diameter

142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum

Chromate

Finish Concealment Covers

Powder coated

Material Type

Aluminum | Steel

Environmental Specifications

Thermal Compliance

GR-487

Packaging and Weights

Volume

0.27 m³ | 9.52 ft³

Weight (unloaded)

34.019 kg | 75 lb

* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines