


UQXRZLU7R



Ultra Low Loss (ULL) OM4 MPO16 APC (Pinned) to LC Uniboot, Fiber Array Cable Assembly, 16-Fiber, Plenum

Product Classification

Regional Availability	Asia Australia/New Zealand China Europe India Latin America Middle East/Africa North America
Portfolio	CommScope®
Product Type	Fiber array cable assembly
Product Brand	Propel SYSTIMAX ULL
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Connector A, quantity	1
Color, boot A	Black
Color, connector A	Green
Connector B, quantity	16
Color, boot B	Aqua
Color, connector B	Green
Construction Type	Stranded
Fibers per Subunit, quantity	16
Furcation Color	Aqua
Interface, Connector A	MPO-16/APC Male
Interface, Connector B	LC/UPC
Interface Feature, connector B	Uniboot
Jacket Color	Aqua
Polarity	Method B Enhanced (ULL)
Total Fibers, quantity	16

Dimensions

UQXRZLU7R

Breakout Length	12 in 24 in 36 in 48 in 60 in 72 in
Cable Assembly Length Range (m)	1 – 304
Cable Assembly Length Range (ft)	2 – 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum	11.24 lb @ 0 ° 4.40 lb @ 90 °
-----------------------------------	---------------------------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, LazrSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Indoor Plenum

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



UQXRZLU7R

Included Products

- | | | |
|-------------------|---|--|
| 760250997 | – | Fiber indoor cable, LazrSPEED® Plenum MPO Light Duty for Patchcords, 16 fiber, Multimode OM4, Feet jacket marking, Aqua jacket color |
| P-016-MP-5K-F30AQ | – | |
| 860658161 | – | 2.0 mm LC/UPC Uniboot GEN 1.5, Aqua |
| 860659158 | – | Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable |