

Arrestor Plus® Dual Band Quarterwave Surge Arrestor (T-shaped, Cylindrical), 800–2170 MHz, with interface types N Female and N Female

Product Classification


Product Type	Surge arrestor
Product Brand	Arrestor Plus®
Ordering Note	CommScope® non-standard product
General Specifications	
Device Type	dc Block
Inner Contact Plating	Gold
Interface	N Female
Interface 2	N Female
Outer Contact Plating	Trimetal
Pressurizable	No
Dimensions	
Height	74 mm 2.913 in
Width	25 mm 0.984 in
Length	73 mm 2.874 in

Outline Drawing

Page 1 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024





Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss, typical	0.07 dB
Average Power at Frequency	600.0 W @ 900 MHz
Connector Impedance	50 ohm
Lightning Surge Capability	100 times @ 20 kA
Lightning Surge Capability Test Method	IEEE C62.42-1991
Lightning Surge Capability Waveform	8/20 waveform
Lightning Surge Current	30 kA
Lightning Surge Current Waveform	8/20 waveform
Operating Frequency Band	1710 – 2000 MHz 2000 – 2170 MHz 806 – 824 MHz 824 – 960 MHz
Peak Power, maximum	10 kW
Throughput Energy at Current	2.0 mJ @ 30 kA 25.0 μJ @ 2 kA
Throughput Energy Waveform	8/20 waveform

Page 2 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

COMMSCOPE°

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
806-824 MHz	1.152	23.02
824–960 MHz	1.135	23.98
1710–2000 MHz	1.101	26.36
2000–2170 MHz	1.135	23.98

Mechanical Specifications

Attachment Durability	25 cycles
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5
Mechanical Shock Test Method	MIL-STD-202F, Method 213B, Test Condition C

Environmental Specifications

Storage Temperature -40 °C to +100 °C (-40 °F to +212 °F)
Attenuation, Ambient Temperature 20 °C 68 °F
Average Power, Ambient Temperature40 °C 104 °F
Corrosion Test Method MIL-STD-202, Method 101, Test Condition B
Immersion Depth 1 m
Immersion Test Mating Mated
Immersion Test Method IEC 60529:2001, IP68
Moisture Resistance Test MethodMIL-STD-202, Method 106
Thermal Shock Test MethodMIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
Vibration Test MethodGR 2846-CORE
Water Jetting Test Mating Mated

Packaging and Weights

Weight, net

0.399 kg | 0.88 lb

Regulatory Compliance/Certifications

Classification

Agency

CHINA-ROHS

Above maximum concentration value

Page 3 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024



ISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliant/ExemptedUK-ROHSCompliant/Exempted



* Footnotes

Immersion Depth

Insertion Loss, typical

0.05√⁻freq (GHz) (not applicable for elliptical waveguide) Immersion at specified depth for 24 hours

Page 4 of 4

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 21, 2024

