3399105 | 125T(TD)135WP1250TAPE



Toneable ConQuest® Empty Conduit, 1 1/4 in, SDR 13.5, terracotta, with pull tape

Product Classification

Product TypeEmpty conduitProduct BrandConQuest®

General Specifications

ColorTerracottaConductor Elongation, maximum30 %Conductor TypeSolid

Conduit Type Toneable

Density Test Method ASTM D792A

 Density, maximum
 0.955 g/cm³ | 0.035 lb/in³

 Density, minimum
 0.941 g/cm³ | 0.034 lb/in³

Design Standard ASTM D3350-05

Wall Type Smooth

Dimensions

 Length
 914.4 m | 3000 ft

 Conductor Diameter
 1.024 mm | 0.04 in

 Inner Diameter, nominal
 35.408 mm | 1.394 in

 Outer Diameter, nominal
 42.164 mm | 1.66 in

Wall Thickness Designation SDR 13.5

Wall Thickness, minimum 3.124 mm | 0.123 in

Nominal Size 1-1/4 in Conductor Gauge 18 AWG

Electrical Specifications

Conductor Resistance 98.425 ohms/km | 30 ohms/kft



3399105 | 125T(TD)135WP1250TAPE

Material Specifications

Conductor Material Type Copper-clad steel (CCS)

Flexural Modulus, minimum 551.581 N/mm² | 80000 psi

Flexural Property Test Method ASTM D790

Hydrostatic Design BasisNot pressure rated

Hydrostatic Design Test MethodASTM D2837

Material Type High density polyethylene (HDPE) | Polyester

Melt Flow Rate Test MethodASTM D1238Melt Flow Rate, maximum0.39 g/10 min

Mechanical Specifications

Minimum Bend Radius, unsupported 457.2 mm | 18 in

Tensile Property Test Method ASTM D638

Tensile Strength at yield, minimum 20.684 N/mm² | 3000 psi

Breaking Strength 566.99 kg | 1250 lb

Conductor Tensile Strength, minimum 344.738 N/mm² | 50000 psi

Pull Line Type Tape

Pulling Tension Note Applies to products manufactured after December 31, 2012

Pulling Tension, maximum 571.526 kg | 1260 lb

Environmental Specifications

Environmental Stress Crack Resistance Failure rate of 10% within 96 hours

Environmental Stress Test Method ASTM D1693, ESCR Condition B

Packaging and Weights

Weight, net 394.363 kg/km | 265 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



* Footnotes



3399105 | 125T(TD)135WP1250TAPE

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistence