810010160/DB | 0-036-DF-HY-F36NS/30T /8W036/1X24AWG/200



LightScope ZWP® Fiber + Tone Wire Outdoor Drop Cable, 36 fiber Arid Core construction, central loose tube

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Hybrid cable, fiber and tone-wire

Product Brand LightScope ZWP®

Government Funding Build America Buy America (BABA) compliant*

General Specifications

Cable TypeCentral loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Jacket Color Black

Subunit, quantity 3

Fibers per Subunit, quantity 12

Tone Wire, quantity

Total Fiber Count 36

Dimensions

Height Over Jacket 4.572 mm | 0.18 in

Buffer Tube/Subunit Diameter 3.048 mm | 0.12 in

Diameter Over Jacket 9.906 mm | 0.39 in


Diameter Over Messenger Jacket 2.032 mm | 0.08 in

Tone Wire Gauge 24 AWG

Representative Image

COMMSCOPE®

810010160/DB | 0-036-DF-HY-F36NS/30T /8W036/1X24AWG/200



Mechanical Specifications

Minimum Bend Radius, loaded86.36 mm3.4 inMinimum Bend Radius, unloaded63.5 mm2.5 in

Tensile Load, long term, maximum 400.34 N | 90 lbf

Tensile Load, short term, maximum 1,334.466 N | 300 lbf

Compression 1.018 kg/mm | 57 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 35 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 2.17 ft lb | 2.942 N-m

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 889.102 m | 2917 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications



810010160/DB | 0-036-DF-HY-F36NS/30T /8W036/1X24AWG/200

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 °F to +167 °F)

Cable Qualification StandardsANSI/ICEA S-110-717Environmental SpaceAerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penentration 24 h

Water Penentration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 70 °C | 158 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 36.906 kg/km | 24.8 lb/kft

Included Products

CS-8S-200UM-LT – 200 Micron Low Macrobending, Dispersion-Unshifted OS2 Singlemode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8S-200UM-LT

200 Micron Low Macrobending, Dispersion-Unshifted OS2 Singlemode Fiber

Product Classification

Portfolio CommScope® **Product Type** Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.7 µm 0.7 % **Cladding Non-Circularity, maximum Coating Diameter (Colored)** 200 um **Coating Diameter (Uncolored)** 190 µm **Coating Diameter Tolerance (Colored)** ±10 μm **Coating Diameter Tolerance (Uncolored)** ±10 μm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm Core/Clad Offset, maximum

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

Macrobending, 20 mm Ø mandrel, 1 turn 0.75 dB @ 1,550 nm | 1.50 dB @ 1,625 nm Macrobending, 30 mm Ø mandrel, 10 turns 0.25 dB @ 1,550 nm | 1.00 dB @ 1,625 nm

 $0.5 \, \mu m$

Macrobending, 50 mm Ø mandrel, 100 turns 0.05 dB @ 1,550 nm Coating Strip Force, maximum 8.9 N | 2.001 lbf **Coating Strip Force, minimum** 0.5 N | 0.112 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum 1260 nm Point Defects, maximum 0.1 dB

COMMSCOPE®

CS-8S-200UM-LT

Zero Dispersion Slope, maximum 0.09 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1320 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.25 dB/km @ 1,550 nm | 0.27 dB/km @ 1,490

nm | 0.27 dB/km @ 1,625 nm | 0.33 dB/km @ 1,385

nm | 0.36 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.467 @ 1,550

nm

 Mode Field Diameter
 8.6 μm @ 1,310 nm | 9.8 μm @ 1,550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.1 ps/sqrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS2)

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

