


MC-RMHD-1545-4

Universal Ring Mount, Heavy Duty 4-sector, 12 in to 45 in OD



Product Classification

Product Type Universal ring mount

General Specifications

Mounting Monopole, 304.8–1270 mm (12–50 in) OD

Pipe, quantity 0

Sectors, quantity 4

Dimensions

Mounting Diameter, maximum 1,143 mm | 45 in

Mounting Diameter, minimum 304.8 mm | 12 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Mount | Threaded rod

Packaging quantity 1

Weight, net 183.796 kg | 405.2 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

MC-RMHD-1545-4

REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

