

DHK-SERIES-HANGER-BLOCKS

Base Product



DHK Series Double Hanger Kits

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™

General Specifications

Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Material Specifications

Material Type	Engineered plastic Stainless steel
----------------------	--------------------------------------

Mechanical Specifications

Vibration Survival	≥4 hours at resonant frequency
---------------------------	--------------------------------

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Corrosion Resistance, minimum with no degradation	≥500 hours in salt spray chamber
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥100 hours exposure in accelerated UV life chamber