

SURGE-ARRESTORS

Base Product



Arrestor Plus® Dual Band Quarterwave and Gas Tube Surge Arrestors

Product Classification

Product Type	Surge arrestor
Product Brand	Arrestor Plus®

Electrical Specifications

Connector Impedance	50 ohm
Lightning Surge Current Waveform	8/20 waveform

Mechanical Specifications

Interface Durability Method	IEC 61169-16:9.5
------------------------------------	------------------

Environmental Specifications

Attenuation, Ambient Temperature	20 °C 68 °F
Average Power, Ambient Temperature	40 °C 104 °F
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68