

# R-002-ZC-8F-F16

---

Fiber indoor cable, Riser Zipcord, 2 fiber, Singlemode G.657.A1, 1.6 mm diameter, Feet jacket marking

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   Latin America   Middle East/Africa   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | R-ZC  |


## General Specifications

|                             |             |
|-----------------------------|-------------|
| <b>Cable Type</b>           | Cordage     |
| <b>Construction Type</b>    | Non-armored |
| <b>Fiber Type, quantity</b> | 2           |
| <b>Jacket Marking</b>       | Feet        |
| <b>Subunit Type</b>         | Gel-free    |
| <b>Total Fiber Count</b>    | 2           |

## Dimensions

|                           |                   |
|---------------------------|-------------------|
| <b>Height Over Jacket</b> | 1.7 mm   0.067 in |
| <b>Width Over Jacket</b>  | 3.5 mm   0.138 in |

## Representative Image



# R-002-ZC-8F-F16

---

## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 38 mm   1.496 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 15 mm   0.591 in                      |
| <b>Tensile Load, long term, maximum</b>  | 53 N   11.915 lbf                     |
| <b>Tensile Load, short term, maximum</b> | 178 N   40.016 lbf                    |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 300 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 0.74 N-m   6.55 in lb                 |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Environmental Specifications

|                                      |                                       |
|--------------------------------------|---------------------------------------|
| <b>Installation temperature</b>      | -20 °C to +70 °C (-4 °F to +158 °F)   |
| <b>Operating Temperature</b>         | -20 °C to +70 °C (-4 °F to +158 °F)   |
| <b>Storage Temperature</b>           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>Environmental Space</b>           | Riser                                 |
| <b>Flame Test Listing</b>            | NEC OFNR (ETL) and c(ETL)             |
| <b>Flame Test Method</b>             | UL 1666                               |

## Environmental Test Specifications

|                                  |                                     |
|----------------------------------|-------------------------------------|
| <b>Heat Age</b>                  | -20 °C to +85 °C (-4 °F to +185 °F) |
| <b>Heat Age Test Method</b>      | IEC 60794-1 F9                      |
| <b>Low High Bend</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Low High Bend Test Method</b> | FOTP-37   IEC 60794-1 E11           |
| <b>Temperature Cycle</b>         | -20 °C to +70 °C (-4 °F to +158 °F) |

# R-002-ZC-8F-F16

---

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

## Packaging and Weights

**Cable weight** 5.8 kg/km | 3.897 lb/kft

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## Included Products

CS-8F-TB – Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable