


# 760004242 | N-006-DS-8W-FSUYL/D

---



Fiber indoor cable, TeraSPEED® Low Smoke Zero Halogen Riser Distribution, 6 fiber single-unit, Singlemode G.652.D and G.657.A1, Feet jacket marking, Yellow jacket color, Dca flame rating

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | N-DS  |

## General Specifications

|                          |              |
|--------------------------|--------------|
| <b>Cable Type</b>        | Distribution |
| <b>Construction Type</b> | Non-armored  |
| <b>Subunit Type</b>      | Gel-free     |
| <b>Jacket Color</b>      | Yellow       |
| <b>Jacket Marking</b>    | Feet         |
| <b>Total Fiber Count</b> | 6            |

## Dimensions

|                             |                  |
|-----------------------------|------------------|
| <b>Diameter Over Jacket</b> | 5.07 mm   0.2 in |
|-----------------------------|------------------|

## Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 76 mm   2.992 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 51 mm   2.008 in                      |
| <b>Tensile Load, long term, maximum</b>  | 200 N   44.962 lbf                    |
| <b>Tensile Load, short term, maximum</b> | 667 N   149.948 lbf                   |
| <b>Compression</b>                       | 10 N/mm   57.101 lb/in                |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 100 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 2.94 N-m   26.021 in lb               |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Optical Specifications

|                   |                                  |
|-------------------|----------------------------------|
| <b>Fiber Type</b> | G.652.D and G.657.A1, TeraSPEED® |
|-------------------|----------------------------------|

## Environmental Specifications

# 760004242 | N-006-DS-8W-FSUYL/D

|   |   |
|---|---|
| <b>Installation temperature</b>                     | -10 °C to +60 °C (+14 °F to +140 °F)                        |
| <b>Operating Temperature</b>                        | -20 °C to +70 °C (-4 °F to +158 °F)                         |
| <b>Storage Temperature</b>                          | -40 °C to +70 °C (-40 °F to +158 °F)                        |
| <b>Cable Qualification Standards</b>                | ANSI/ICEA S-83-596   Telcordia GR-409                       |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | Dca   |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1a   |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d1  |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a2  |
| <b>Environmental Space</b>                          | Low Smoke Zero Halogen (LSZH)   Riser                       |
| <b>Flame Test Listing</b>                           | NEC OFNR-ST1 (ETL) and c(ETL)                               |
| <b>Flame Test Method</b>                            | IEC 60332-3   IEC 60754-2   IEC 61034-2   UL 1666   UL 1685 |

## Environmental Test Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Heat Age</b>                      | -20 °C to +85 °C (-4 °F to +185 °F)  |
| <b>Heat Age Test Method</b>          | IEC 60794-1 F9                       |
| <b>Low High Bend</b>                 | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11            |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F)  |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1              |

## Packaging and Weights

|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 24 kg/km   16.127 lb/kft |
|---------------------|--------------------------|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CENELEC       | EN 50575 compliant, Declaration of Performance (DoP) available   |
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |



## Included Products

CS-8W-TB – TeraSPEED® Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## TeraSPEED®

## TeraSPEED® Singlemode Fiber

### Product Classification

|                     |               |
|---------------------|---------------|
| <b>Portfolio</b>    | CommScope®    |
| <b>Product Type</b> | Optical fiber |

### General Specifications

|  |  |
|--|--|
| <b>Cladding Diameter</b>                             | 125 µm                                 |
| <b>Cladding Diameter Tolerance</b>                   | ±0.7 µm                                |
| <b>Cladding Non-Circularity, maximum</b>             | 0.7 %                                  |
| <b>Coating Diameter (Colored)</b>                    | 249 µm                                 |
| <b>Coating Diameter (Uncolored)</b>                  | 242 µm                                 |
| <b>Coating Diameter Tolerance (Colored)</b>          | ±13 µm                                 |
| <b>Coating Diameter Tolerance (Uncolored)</b>        | ±5 µm                                  |
| <b>Coating/Cladding Concentricity Error, maximum</b> | 12 µm                                  |
| <b>Core Diameter</b>                                 | 8.3 µm                                 |
| <b>Core/Clad Offset, maximum</b>                     | 0.5 µm                                 |
| <b>Proof Test</b>                                    | 689.476 N/mm <sup>2</sup>   100000 psi |
| <b>Tight Buffer Diameter</b>                         | 900 µm                                 |
| <b>Tight Buffer Diameter Tolerance</b>               | ±40 µm                                 |

### Dimensions

|                            |                 |
|----------------------------|-----------------|
| <b>Fiber Curl, minimum</b> | 4 m   13.123 ft |
|----------------------------|-----------------|

### Mechanical Specifications

|   |   |
|---|---|
| <b>Macrobending, 20 mm Ø mandrel, 1 turn</b>    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| <b>Macrobending, 30 mm Ø mandrel, 10 turns</b>  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| <b>Macrobending, 60 mm Ø mandrel, 100 turns</b> | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| <b>Coating Strip Force, maximum</b>             | 8.9 N   2.001 lbf                       |
| <b>Coating Strip Force, minimum</b>             | 1.3 N   0.292 lbf                       |

# CS-8W-TB

**Dynamic Fatigue Parameter, minimum** 20

## Optical Specifications

**Cabled Cutoff Wavelength, maximum** 1260 nm

**Point Defects, maximum** 0.1 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1324 nm

**Zero Dispersion Wavelength, minimum** 1300 nm

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.50 dB/km @ 1,310 nm | 0.50 dB/km @ 1,385 nm | 0.50 dB/km @ 1,490 nm | 0.50 dB/km @ 1,550 nm | 0.50 dB/km @ 1,575 nm | 0.70 dB/km @ 1,270 nm

**Backscatter Coefficient** -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550 nm

**Mode Field Diameter** 10.4  $\mu\text{m}$  @ 1,550 nm | 9.2  $\mu\text{m}$  @ 1,310 nm | 9.6  $\mu\text{m}$  @ 1,385 nm

**Mode Field Diameter Tolerance**  $\pm 0.4 \mu\text{m}$  @ 1310 nm |  $\pm 0.5 \mu\text{m}$  @ 1550 nm |  $\pm 0.6 \mu\text{m}$  @ 1385 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.04 ps/sqrt(km)

**Standards Compliance** ITU-T G.652.D | ITU-T G.657.A1 | TIA-492CAAB (OS1a)

## Environmental Specifications

**Heat Aging, maximum** 0.05 dB/km @ 85 °C

**Temperature Dependence, maximum** 0.05 dB/km

**Temperature Humidity Cycling, maximum** 0.05 dB/km

**Water Immersion, maximum** 0.05 dB/km @ 23 °C

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

# CS-8W-TB

---

**Temperature Dependence, maximum**

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum**

Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity