760234195 | HTC-4SM-410-APVA

HELIAX® Hybrid Cable, UL Type TC-OF-ER

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Hybrid cable, copper and fiber

Product Brand HELIAX®

General Specifications

Application Remote radio head

Cable Type Wireless feeder

Conductors, quantity 4

Construction Type Shielded

Fiber Short Description RFF – 10AWG

Fiber Type, quantity 4

Fibers per Subunit, quantity 2

Inner Shield (Tape) Material Corrugated aluminum

Jacket Color Black

Outer Shield (Tape) Material PVC

Strength Members Glass reinforced plastic rod

Subunit, quantity 2
Total Fiber Count 4

Dimensions

Buffer Tube/Subunit Diameter3.556 mm | 0.14 inDiameter Over Jacket18.288 mm | 0.72 in

Conductor Gauge 10 AWG

Electrical Specifications


dc Resistance Note Maximum value based on a standard condition of 20 °C (68 °F)

dc Resistance, maximum 3.409 ohms/km | 1.039 ohms/kft



760234195 | HTC-4SM-410-APVA

Representative Image



Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded 365.76 mm | 14.4 in

Minimum Bend Radius, multiple bends, unloaded 220.98 mm | 8.7 in

Minimum Bend Radius, single bend, unloaded 127 mm | 5 in

Tensile Load, long term, maximum 800.68 N | 180 lbf

Tensile Load, short term, maximum 2,668.932 N | 600 lbf

Compression 2.25 kg/mm | 126 lb/in

Compression Test Method FOTP-41

Flex 25 cycles

Flex Test Method FOTP-104

Impact 2.17 ft lb | 2.942 N-m

Impact Test Method FOTP-25

Twist 10 cycles

Twist Test Method FOTP-85

Optical Specifications

Fiber Type G.657.A2/B2 | G.657.A2/B2

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | Telcordia GR-20 | Telcordia GR-409

Page 2 of 5



760234195 | HTC-4SM-410-APVA

Environmental Space

Wireless installation

Packaging and Weights

Cable weight 456.122 kg/km | 306.5 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



Included Products

CS-8G-MP – Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T

G.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



CS-8G-MP

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm ±0.7 µm **Cladding Diameter Tolerance Cladding Non-Circularity, maximum** 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 µm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum $0.5 \, \mu m$

Proof Test 689.476 N/mm² | 100000 psi

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 15 mm mandrel, 1 turn
 0.50 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 20 mm mandrel, 1 turn
 0.10 dB @ 1,550 nm
 | 0.20 dB @ 1,625 nm

 Macrobending, 30 mm mandrel, 10 turns
 0.03 dB @ 1,550 nm
 | 0.10 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

COMMSCOPE®

CS-8G-MP

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1302 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.40 dB/km @ 1,310 nm | 0.40 dB/km @ 1,385

nm | 0.40 dB/km @ 1,550 nm | 0.50 dB/km @ 1,625

nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 Mode Field Diameter
 8.6 μm @ 1,310 nm | 9.8 μm @ 1,550 nm

Mode Field Diameter Tolerance $\pm 0.4 \,\mu\text{m}$ @ 1310 nm | $\pm 0.5 \,\mu\text{m}$ @ 1550 nm

Polarization Mode Dispersion Link Design Value, maximum 0.06 ps/sqrt(km)

Standards Compliance ITU-T G.657.A2 | ITU-T G.657.B2

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

Temperature Dependence, maximum0.05 dB/kmTemperature Humidity Cycling, maximum0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

COMMSCOPE®