


HFC-16MM-806-618-APE



HELIAX® LazrSPEED® Hybrid Cable with aluminum armor

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Hybrid cable, copper and fiber
Product Brand	HELIAX® LazrSPEED®

General Specifications

Application	Remote radio head
Alarm Wire, quantity	6
Armor Type	Corrugated aluminum
Cable Type	Wireless feeder
Conductors, quantity	8
Construction Type	Armored
Fiber Short Description	RFF – 6AWG
Fiber Type, quantity	16
Fibers per Subunit, quantity	8
Inner Shield (Tape) Material	Corrugated aluminum
Jacket Color	Black
Outer Shield (Tape) Material	PE
Strength Members	Glass reinforced plastic rod
Subunit, quantity	2
Total Fiber Count	16
Water Blocking Method	Water blocking tape(s) Water blocking threads

HFC-16MM-806-618-APE


Dimensions

Buffer Tube/Subunit Diameter	6.096 mm 0.24 in
Diameter Over Jacket	30.734 mm 1.21 in
Alarm Wire Gauge	18 AWG
Conductor Gauge	6 AWG

Electrical Specifications

dc Resistance Note	Maximum value based on a standard condition of 20 °C (68 °F)
dc Resistance, maximum	1.352 ohms/km 0.412 ohms/kft

Representative Image



Material Specifications

Ripcord Material	Para-aramid synthetic fiber
-------------------------	-----------------------------

Mechanical Specifications

Minimum Bend Radius, multiple bends, loaded	614.68 mm 24.2 in
Minimum Bend Radius, multiple bends, unloaded	307.34 mm 12.1 in
Minimum Bend Radius, single bend, unloaded	215.9 mm 8.5 in
Tensile Load, long term, maximum	1,067.573 N 240 lbf
Tensile Load, short term, maximum	3,558.576 N 800 lbf
Compression	2.25 kg/mm 126 lb/in
Compression Test Method	FOTP-41
Flex Test Method	FOTP-104
Impact	2.17 ft lb 2.942 N-m
Impact Test Method	FOTP-25

HFC-16MM-806-618-APE

Twist	10 cycles
Twist Test Method	FOTP-85

Optical Specifications

Fiber Type	OM2+, LazrSPEED® 150 OM2+, LazrSPEED® 150
-------------------	---

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640 Telcordia GR-20 Telcordia GR-409
Environmental Space	Wireless installation

Packaging and Weights

Cable weight	1,616.146 kg/km 1086 lb/kft
---------------------	-------------------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5M-MP	– LazrSPEED® 150 OM2+ Bend-Insensitive Multimode Fiber
----------	--

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable