

A-100872

Base Product



Three Phase Meter Cabinet with Generator

- Sealed to outside environment
- Double wall construction

Product Classification

Product Type

Power supply enclosure

General Specifications

Access

Front door

Accessories

Cable plate | In-ground root | Plinth

Batteries Supported

0

Batteries Supported, with optional battery pedestal

0

Cabinet Type

Meter cabinet

Color

Green | Green (RAL 6009) | Light Gray (RAL 7035) | Others available at additional cost

Door Security

7 mm triangle lock

Internal Mounting Surface

12 mm plywood backboard

Dimensions

Height

1016 mm | 40 in

Width

660.4 mm | 26 in

Depth

254 mm | 10 in

Depth, without door

254 mm | 10 in

Electrical Specifications

ac Distribution Type

20-way metal enclosure

ac Feeds, Outgoing, quantity

6

Generator Connection

125 A three phase

Power Phase

Three

Voltage

415 Vac

Material Specifications

A-100872

Finish Powder coated

Material Type Galvanized steel

Packaging and Weights

Weight, net 35.834 kg | 79 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system