J96345-000 | OCM1-CYC47AL1



OCM1 LGX Fiber Optic Module, CWDM, Double Mux, LC/UPC, 8 channels, upgrade port, 1310 nm port, starting wavelength 1470 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Double multiplexing
Technology Type	Thin film filter (TFF)
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, front	LC/UPC
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Multiplexers, quantity	1
Port Type, optional	1310 nm port Upgrade port
Dimensions	

Height	129.54 mm 5.1 in
Width	27.94 mm 1.1 in
Depth	127 mm 5 in

Optical Specifications

Channel Spacing	Skipped channels
Starting Wavelength	1470 nm

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 22, 2023



J96345-000 | OCM1-CYC47AL1

Packaging and Weights

Packaging quantity

Packaging Type

Box | Carton

Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 22, 2023

