

FDT-CJ048NXT6000



iFDT Indoor Fiber Distribution Terminal, 48-fiber, SC/APC, loose tube OSP cable, 6000 feet

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

| | |
|------------------------------|-----------------------------|
| Regional Availability | North America |
| Product Type | Fiber distribution terminal |
| Product Series | IFDT |

General Specifications

| | |
|-----------------------------|--------------------------|
| Adapters, quantity | 48 |
| Cable Entry Location | Bottom right Top right |
| Cable Type | OSP - Loose Tube |
| Color | Putty white |
| Front Door Type | Double hinged |
| Growth Configuration | Fully loaded |
| Interface | SC/APC |
| Interface, stub | No connector |
| Lock Type | Padlock ready |
| Mounting | Wall |
| Port, quantity | 48 |

Dimensions

| | |
|---------------------|----------------------|
| Height | 476.25 mm 18.75 in |
| Width | 368.3 mm 14.5 in |
| Depth | 127 mm 5 in |
| Cable Length | 1,828.8 m 6000 ft |

Ordering Tree

FDT-CJ048NXT6000



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Qualification Standards NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity 1

FDT-CJ048NXT6000

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

