

FDT-DJ272NXB0000



iFDT Indoor Fiber Distribution Terminal, 72-fiber, SC/APC, soft-wall pigtailed, heat shrink splice trays

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications


Functionality	Patching Splicing
Adapters, quantity	72
Cable Entry Location	Bottom right Top right
Cable Type	Pigtails - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	SC/APC
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	72
Splice Tray Chip Type	Heat shrink
Splicing Capacity, maximum	72

Dimensions

Height	599.44 mm 23.6 in
Width	369.82 mm 14.56 in
Depth	127 mm 5 in

FDT-DJ272NXB0000

Ordering Tree



Material Specifications

- Finish** Powder coated
- Material Type** Steel

Optical Specifications

- Fiber Mode** Singlemode

Environmental Specifications

- Environmental Space** Indoor
- Qualification Standards** NEMA, Type 12 | Telcordia GR-2898-CORE

Packaging and Weights

- Packaging quantity** 1

FDT-DJ272NXB0000

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

