760209957 | HD-2U



High Density 2U modular cassette sliding Panel, accepts (8) G2 modules or MPO panels, providing up to 96 duplex LC ports or up to 64 MPO ports

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®
Product Type Fiber patch panel

Product Series HD

General Specifications

Application Accepts eight G2 modular cassettes

Color Black + Silver gray (front)

Intelligence Type iPatch® ready

Interface, frontUnloadedRack TypeEIA 19 in

Rack Units 2

Shelf Movement Sliding

Total Ports, quantity 0

Dimensions

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

 Depth
 549.91 mm | 21.65 in

Material Specifications

Material Type Steel

Environmental Specifications

Flammability Rating UL 94 V-0
Safety Standard UL 1863

COMMSCOPE®

760209957 | HD-2U

Packaging and Weights

Packaging quantity 1

Weight, net 7.711 kg | 17 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

