

NG4-VCKR2F47001K



NG4access® Module VAM, CWDM, 8 channels, 1310 nm port, 2 circuits, LC/UPC, right, 1471 nm starting channel, 1 test port

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Brand	NG4access®
Product Series	NG4

General Specifications

Device Type	Plug-and-play module
Functionality	Multiplexing
Application	For use with NG4 access frames
Circuits, quantity	2
Distribution Type	8-channel CWDM
Interface, front	LC/UPC
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Multiplexers, quantity	2
Port Type, optional	1310 nm port Test port
Tray Orientation	Right orientation

Dimensions

Height	13.21 mm 0.52 in
Width	159.77 mm 6.29 in
Depth	130.3 mm 5.13 in

NG4-VCKR2F47001K

Optical Specifications

Starting Channel Number	47
Starting Wavelength	1471 nm

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

