



iPatch® 600A Fixed Single-mode Intelligent Fiber Panel, SC 12 port duplex

OBSOLETE

This product was discontinued on: December 31, 2012

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Brand	iPatch®

General Specifications

Color	Black
Intelligence Type	iPatch® enabled
Interface, front	SC
Rack Units	1
Shelf Movement	Fixed
Total Ports, quantity	12

Dimensions

Height	44.45 mm 1.75 in
Width	482.6 mm 19 in
Depth	223.52 mm 8.8 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)
----------------------	--

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

760010777 | iP-600A-12-SC-SMF

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE CSA UL

Packaging and Weights

Included	Cover Four #12-24 mounting screws Instruction sheet One piece double sided tape One set splice tray holders Shelf Two cable ties Two wire retainers
Packaging quantity	1
Weight, net	1.814 kg 4 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

