

760169193 | 360G2-iP-2U-96-MPO-DP-UHD

SYSTIMAX 360™ iPatch® G2 2U 96-MPO Distribution Panel, UHD Panel

OBSOLETE

Replaced By:

760236362 UD iPATCH 2U 96-MPO Distribution Panel, Sliding Panel
UD-iP-2U-96-MPO-DP-SD

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber splice panel |
| Product Brand | LazrSPEED® SYSTIMAX 360™ iPatch® |

General Specifications

| | |
|------------------------------|-----------------|
| Color | Black |
| Intelligence Type | iPatch® enabled |
| Interface, front | MPO |
| Rack Units | 2 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 96 |

Dimensions

| | |
|---------------|---------------------|
| Height | 88.9 mm 3.5 in |
| Width | 482.6 mm 19 in |
| Depth | 492.76 mm 19.4 in |

Material Specifications

| | |
|----------------------|--|
| Material Type | Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) |
|----------------------|--|

Optical Specifications

| | |
|-------------------|------------------------|
| Fiber Mode | Multimode Singlemode |
|-------------------|------------------------|

Environmental Specifications

760169193 | 360G2-iP-2U-96-MPO-DP-UHD

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Flammability Rating | UL 94 V-0 |
| Safety Standard | Austel CE CSA UL |

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

