

EG9081-000 | OCM1-CC8471S2



OCM1 LGX Fiber Optic Module, CWDM, Compact, SC/APC, 8 channels, starting wavelength 1470 nm

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	LGX OCM1

General Specifications

Device Type	Standard VAM
Functionality	Multiplexing
Technology Type	Thin film filter (TFF)
Application	For use with LGX panels
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Multiplexers, quantity	1

Dimensions

Height	129.54 mm 5.1 in
Width	58.42 mm 2.3 in
Depth	127 mm 5 in

Optical Specifications

Channel Spacing	20 nm
Starting Wavelength	1470 nm

Packaging and Weights

Packaging quantity 1
Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant/Exempted

