652598-000 | OCM1-CYC471L1



OCM1 LGX Fiber Optic Module, CWDM, Double Mux, LC/UPC, 8 channels, upgrade port, 1310 nm port, starting wavelength 1470 nm

Product Classification

Regional AvailabilityNorth AmericaPortfolioCommScope®Product TypeCWDM moduleProduct SeriesLGX | OCM1

General Specifications

Device Type Standard VAM

 Functionality
 Double multiplexing

 Technology Type
 Thin film filter (TFF)

Application For use with LGX panels

Circuits, quantity 1

Distribution Type 8-channel CWDM

Interface, frontLC/UPCInterface, InputLC/UPCInterface, OutputLC/UPC

Multiplexers, quantity 1

Port Type, optional 1310 nm port | Upgrade port

Dimensions

 Height
 129.54 mm | 5.1 in

 Width
 27.94 mm | 1.1 in

 Depth
 127 mm | 5 in

Optical Specifications

Channel Spacing 20 nm Starting Wavelength 1470 nm

COMMSCOPE®

652598-000 | OCM1-CYC471L1

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

