760102269 | 360-PM-GS3-DM6



SYSTIMAX 360™ GigaSPEED XL® PATCHMAX® GS3 Distribution Module, 6 port

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type Module

Product Brand GigaSPEED XL® | PATCHMAX® | SYSTIMAX 360™

General Specifications

ANSI/TIA Category 6

Cable TypeUnshieldedColorCool gray

Conductor Type Solid | Stranded

Intelligence Type iPatch® ready

Modules, quantity 1
Termination Type IDC
Total Ports, quantity 6

Wiring T568A | T568B

Dimensions

Compatible Diameter Over Dielectric, maximum1.168 mm | 0.046 inCompatible Diameter Over Dielectric, minimum0.762 mm | 0.03 in

Compatible Conductor Gauge, solid 22-24 AWG | 21 AWG (for CommScope GigaREACH cable

only)

Compatible Conductor Gauge, stranded 22–24 AWG

Electrical Specifications



760102269 | 360-PM-GS3-DM6

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Material Specifications

Contact Plating Material Precious metals

Material Type High-impact, flame retardant, thermoplastic

Termination Contact Plating Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133.447 N | 30 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant



