

760231480 | SD-2U-FX

Standard Density 2U fixed Panel, accepts (6) LGX/1000 style footprint modules or panels, providing up to 72 duplex LC ports



OBSOLETE

This product was discontinued on: October 31, 2022

Replaced By:

760251047 EPX 2U fixed panel, accepts (6) LGX/PNL style splice cassettes, modules or panels, providing up to 72
EPX-2U-PNL-ENC-FX duplex LC ports

Product Classification

Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	SD

General Specifications

Application	Accepts six LGX/1000 footprint panels/cassettes
Color	Black
Interface, front	Unloaded
Rack Units	2
Shelf Movement	Fixed

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth	474.98 mm 18.7 in

Material Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC) Steel
----------------------	--

Environmental Specifications

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging quantity 1

Weight, net 6.033 kg | 13.3 lb

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

