760062364 | PM-GS3-48 w/Termination Mgt.



GigaSPEED XL® PATCHMAX® GS3 Category 6 U/UTP Copper Patch Panel, 48 port with termination manager

Available for use with the DYMO® labeling solution

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

Portfolio SYSTIMAX®

Product Type RJ45 patch panel

Product Brand GigaSPEED XL® | PATCHMAX®

General Specifications

ANSI/TIA Category 6

Cable Type Unshielded

Color Black

Conductor Type Solid | Stranded

Intelligence Type Passive

Modules, quantity 8

Rack Type EIA 19 in

Rack Units 3

Termination Type IDC

Total Ports, quantity 48

Transmission StandardsANSI/TIA-568-D.2 | ISO/IEC 11801 Class E

Wiring T568A | T568B

Dimensions

Height 134.37 mm | 5.29 in

Width 482.6 mm | 19 in

Depth, with cable management 206.5 mm | 8.13 in

Compatible Diameter Over Dielectric, maximum 1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum 0.762 mm | 0.03 in

COMMSCOPE®

760062364 | PM-GS3-48 w/Termination Mgt.

Compatible Conductor Gauge, solid 22-24 AWG | 21 AWG (for CommScope GigaREACH cable

only)

Compatible Conductor Gauge, stranded 22-24 AWG

Electrical Specifications

Current Rating at Temperature $1.5 \text{ A} \otimes 20 \text{ °C} + 1.5 \text{ A} \otimes 68 \text{ °F}$

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Remote Powering Fully complies with the recommendations set forth by IEEE

 $802.3 \rm bt$ (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN

50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Contact Plating Material Precious metals

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

Termination Contact Plating Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

760062364 | PM-GS3-48 w/Termination Mgt.

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

