



Unshielded Distribution Module Wall Mount Panel, Cat 6, 12 port, Black

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	RJ45 patch panel

General Specifications

ANSI/TIA Category	6
Cable Type	Unshielded
Color	Black
Conductor Type	Solid   Stranded
Modules, quantity	2
Panel Style	Straight
Rack Type	EIA 19 in
Termination Type	IDC
Total Ports, quantity	12
Wiring	T568A   T568B

Dimensions

Height	254 mm   10 in
Width	66.04 mm   2.6 in
Depth	91.44 mm   3.6 in
Compatible Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Compatible Diameter Over Dielectric, minimum	0.762 mm   0.03 in
Compatible Conductor Gauge, solid	22 AWG   24 AWG
Compatible Conductor Gauge, stranded	22 AWG   24 AWG

Electrical Specifications

# 760183079 | CPPW-6-DM-12

Current Rating at Temperature	1.5 A @ 20 °C   1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

## Material Specifications

Contact Plating Material	Precious metals
Material Type	High-impact, flame retardant, thermoplastic   Powder-coated steel
Termination Contact Plating	Nickel

## Mechanical Specifications

Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	133 N   29.9 lbf

## Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL   cUL

## Packaging and Weights

Packaging quantity	1
--------------------	---

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

UK-ROHS

Compliant

