



OFDC B8G Fiber Optic Splice/Patch Closure, Gel Cable sealing, 4 pre-installed 12-fiber splice trays, 1 pre-installed 18-fiber splice tray, 8 SC/APC adapters and pigtails

- Advanced gel sealing technology ensures fast and easy field handling without a need for special tools
- Individual access to drop cable connection area and separate zones for looped cable storage for most cable types
- Compact and modular design suited for wraparound drop cable installation, enabling faster deployments
- Allows easy pass-through cabling and integration of optical components, even at later deployment stages

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Single-ended, rectangular fiber closure
Product Series	OFDC

General Specifications

Cable Capacity, Branch	2 Round 8.0–11.0 mm (0.30–0.43 in)
Cable Capacity, Drop	16 Round 1.5–5.5 mm (0.06–0.21 in) 8 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 8 Round 1.5–5.5 mm (0.06–0.21 in)
Cable Capacity, Feeder	2 Round 11.5–15.0 mm (0.45–0.59 in)
Cable Ports Quantity, total	4 round ports + 8 multi-out ports (16 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Manhole Pedestal Strand Wall
Port Type	SC/APC
Port, quantity	8
Splice Tray Included, quantity	5
Splice Tray Type Included	12-way, heat shrink (4) + 18-way, heat shrink (1)
Splicing Capacity, maximum	66
Splicing Type, Supported	Single fusion

760245346 | OFDC-B8G-S2/88-NN-N-66

Splitter Type No splitter

Splitter, quantity 0

Dimensions


Height 128 mm | 5.039 in

Width 156 mm | 6.142 in

Length 324 mm | 12.756 in

Splice Protector Length, maximum 45 mm | 1.772 in

Ordering Tree



Material Specifications

Material Type Rugged polymer

Optical Specifications

Fiber Type G.652.D

Environmental Specifications

Installation temperature -5 °C to +45 °C (+23 °F to +113 °F)

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity 93%, non-condensing

760245346 | OFDC-B8G-S2/88-NN-N-66

Environmental Space	Above ground Below ground
Qualification Standards	IEC 60529, IP68 + 2 m waterhead
UV Resistance	UV stabilized

Packaging and Weights

Included	Fiber pigtail assemblies (8) SC/APC adapters (8)
Packaging quantity	1
Packaging Type	Box Carton
Weight, net	1.85 kg 4.079 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

