



Angled Discrete Distribution Module Panel, Cat6, UTP, 1U, 48 port

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	RJ45 patch panel

## General Specifications

<b>ANSI/TIA Category</b>	6
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Modules, quantity</b>	4
<b>Panel Style</b>	Angled
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	1
<b>Total Ports, quantity</b>	48
<b>Wiring</b>	T568A   T568B

## Dimensions

<b>Height</b>	44.45 mm   1.75 in
<b>Width</b>	482.6 mm   19 in
<b>Depth, with cable management</b>	93.98 mm   3.7 in
<b>Compatible Diameter Over Dielectric, maximum</b>	1.168 mm   0.046 in
<b>Compatible Diameter Over Dielectric, minimum</b>	0.762 mm   0.03 in

## Electrical Specifications

<b>Current Rating at Temperature</b>	1.5 A @ 20 °C   1.5 A @ 68 °F
<b>Dielectric Withstand Voltage, RMS, conductive surface</b>	1,500 Vac @ 60 Hz
<b>Dielectric Withstand Voltage, RMS, contact-to-contact</b>	1,000 Vac @ 60 Hz
<b>Insulation Resistance, minimum</b>	500 MOhm

## Material Specifications

**Material Type** High-impact, flame retardant, thermoplastic | Powder-coated steel

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Storage Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Relative Humidity** Up to 95%, non-condensing

**Flammability Rating** UL 94 V-0

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Modular jacks (48)

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

