

# OTE200-04MH-NN-S12-B-W



Mini-OTE 200-Series, Optical Terminal Enclosure, 4-port full-size connector, no splitter, black, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America
<b>Product Type</b>	Access terminal, without splitter/tap
<b>Product Series</b>	Mini-OTE 200

## General Specifications


<b>Cable Type</b>	No cable (stubless)
<b>Cable, quantity</b>	0
<b>Distribution Type</b>	4 ports
<b>Enclosure Color</b>	Black
<b>Mounting</b>	Handhole   Pole   Wall
<b>Port Type</b>	Hardened full-size SC/APC
<b>Port, quantity</b>	4
<b>Splitter, quantity</b>	0
<b>Stub Type</b>	No tail

## Dimensions


<b>Height</b>	358.5 mm   14.114 in
<b>Width</b>	166 mm   6.535 in
<b>Depth</b>	129.3 mm   5.091 in
<b>Cable Length, stub</b>	0 ft (0 m)

## Dimension Drawing

# OTE200-04MH-NN-S12-B-W



## Ordering Tree



## Material Specifications

### Enclosure Material Type

Glass filled polypropylene (GF-PP)

## Optical Specifications

### Fiber Type

G.652.D

### Operating Wavelength Range

1260 – 1635 nm

### Attenuation Terminal Connectors, maximum

0.4 dB

# OTE200-04MH-NN-S12-B-W

---

<b>Insertion Loss, Terminal Connector, typical</b>	0.16 dB
<b>Return Loss, Connector, minimum</b>	65 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	5%–100%, condensing
<b>Environmental Space</b>	Above ground   Below ground   Buried
<b>Qualification Standards</b>	IEC 60529, IP68 + 3 m waterhead
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Included</b>	Cable termination unit (2)   Enclosure (1)   Fiber pigtail cassette (1)   Splice Cassette (2)
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton


## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## Included Products

CW8094-002 – TENIO™ Cable Termination Unit kit  
TENIO-CTU-L-(10)

## TENIO™ Cable Termination Unit kit



### Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Cable termination kit
<b>Product Series</b>	TENIO

### Environmental Specifications

<b>Environmental Space</b>	Outdoor
----------------------------	---------

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag   Carton

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

