FEC-18-RM



Fiber Optic Entrance Cabinet, 18 Drawers, Rack mounted

- Provides splicing, administration and storage for outside plant (OSP) and intrafacility cables (IFC)
- Offers a cost-effective, space-saving alternative to splicing on the fiber frame
- Cabinets are designed for deployment in a building equipment area
- Bend radius protection and discrete subunit routing paths ensure easy installation
- Can deploy high count of stranded or ribbon fiber cables
- Ultra high density splice capacity dependent on splice tray used

Product Classification

Regional Availability Latin America | North America

Product Type Fiber entrance cabinet

Product Series FEC

General Specifications

Access Front | Rear

Cable Entry LocationBottom | Side | TopCable Exit LocationBottom | Side | Top

Color Putty white

Mounting Rack, EIA 23 in

Splice Drawers, quantity 18
Splice Trays Included, quantity 0

Splicing Capacity Note 18 times number of splices per tray (example 18x288 = 5184)

Dimensions

 Height
 914.4 mm | 36 in

 Width
 660.4 mm | 26 in

 Depth
 381 mm | 15 in

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Included Grommets

COMMSCOPE®

FEC-18-RM

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

