

OTE200-08MX-18-S12-B-W



Mini-OTE 200-Series, Optical Terminal Enclosure, 8-port mini-size connector (DLX®), 1:8 splitter, black, wall mount

- Optical Terminal Enclosures incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Functionality to splice and store feeder cable in the field with the possibility to splice in the field two extra branch cables
- Hardened adapters are factory-terminated and environmentally sealed to ensure rapid plug-and-play drop cable installations
- Integrated external cable fixation guarantees easy, fast and reliable cable manipulations

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America
Product Type	Access terminal, with splitter
Product Brand	DLX®
Product Series	Mini-OTE 200

General Specifications


Cable Type	No cable (stubless)
Cable, quantity	0
Distribution Type	1 x 8 splitter
Enclosure Color	Black
Mounting	Handhole Pole Wall
Port Type	Hardened mini-size DLX
Port, quantity	8
Splitter, quantity	1
Stub Type	No tail

Dimensions


Height	358.5 mm 14.114 in
Width	166 mm 6.535 in
Depth	129.3 mm 5.091 in
Cable Length, stub	0 ft (0 m)

Dimension Drawing

OTE200-08MX-18-S12-B-W



Ordering Tree



Material Specifications

Enclosure Material Type

Glass filled polypropylene (GF-PP)

Optical Specifications

Fiber Type

G.652.D

Operating Wavelength Range

1260 – 1635 nm

Attenuation Splitter, maximum

10.4 dB

OTE200-08MX-18-S12-B-W

Attenuation Terminal Connectors, maximum	0.4 dB
Directivity, minimum	60 dB
Insertion Loss, Splitter, typical	10 dB
Insertion Loss, Terminal Connector, typical	0.16 dB
Return Loss, Connector, minimum	65 dB
Return Loss, Single Ports, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%, condensing
Environmental Space	Above ground Below ground Buried
Qualification Standards	IEC 60529, IP68 + 3 m waterhead
UV Resistance	UV stabilized

Packaging and Weights

Included	Cable termination unit (2) Enclosure (1) Fiber pigtail cassette (1) Optical splitter (1) Splice Cassette (2)
Packaging quantity	1
Packaging Type	Box Carton


Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

CW8094-002 – TENIO™ Cable Termination Unit kit
TENIO-CTU-L-(10)

TENIO™ Cable Termination Unit kit



Product Classification

Regional Availability	EMEA
Product Type	Cable termination kit
Product Series	TENIO

Environmental Specifications

Environmental Space	Outdoor
----------------------------	---------

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

