

C400-NMQM-35

CNT-400 CNT® Jumper with interface types N Male and QMA Male,
10.67 m



Product Classification

Product Type	Braided cable assembly
Product Brand	CNT®
Product Series	CNT-400

General Specifications

Attachment, Connector A	Field attachment
Body Style, Connector A	Straight
Body Style, Connector B	Straight
Cable Family	CNT-400
Interface, Connector A	N Male
Interface, Connector B	QMA Male
Specification Sheet Revision Level	A

Dimensions

Length	10.67 m 35.007 ft
Nominal Size	0.400 in

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
700–3000 MHz	1.433	14.99

Jumper Assembly Sample Label

C400-NMQM-35



Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- | | |
|-------------|---|
| 400APNM-C | - Type N Male for CNT-400 braided cable |
| 400BPNM-C | - Type N Male for CNT-400 braided cable |
| CNT-400 | - CNT-400, CNT® 50 Ohm Braided Coaxial Cable, variable, black PE jacket |
| CNT-400-SFR | - CNT-400-SFR, C CNT® 50 Ohm Braided Coaxial Cable, black non-halogenated, fire retardant polyolefin jacket, B2ca S1a d0 a1 Compliant |
| CNT-400-W | - CNT-400-W, CNT® 50 Ohm Braided Coaxial Cable, variable, white PE jacket |